

# SFK



# DANFOTECH

## SKINKE MASSÉR-MASKINE MASSAGE MACHINE - HAMS



### Beskrivelse

SFK-DANFOTECH's massér-maskine til skinker leveres i rustfri udførelse. Ved anvendelse af rustfri stål til de belastede dele og godkendt polyethylen omkring de bevægelige, er opnået et minimalt støjniveau.

Massér-maskinen kan placeres i eksisterende båndarrangementer, for automatisk kørsel. Der kan leveres nødvendige vende-arrangementer for emnet, alt efter de givne forhold.



### Description

SFK-DANFOTECH's massage machine for hams, is produced of stainless material. Stainless steel is used for the loaded parts, and approved polyethylen for the mobile parts in order to secure a minimal noise-level.

The massage machine can be placed in the existing conveyorarrangements, for automatic carting. Necessary turnarrangements for the subject according to the given conditions, can be delivered.



### Funktionsbeskrivelse



Maskinen består af en drevet underpart og en maserende overdel, der er pneumatisk styret.

Den maserende effekt opnås ved, at skinkerne ruller mellem over og underpart, hvor overparten er trykbelastet. Dette gør, at skinkerne efterfølgende er lettere at udbene.

Massérmaskinen er sikkerhedsmæssigt afskærmet og i overensstemmelse med givne standarder.

### Specifikationer

|   |   |                  |
|---|---|------------------|
| <b>Kapacitet:</b>                         | Ca. 830 stk. pr. time.<br>(830 meter pr. time)  |                  |
| <b>Forbrug:</b>                           | El-spænding 3 x 380-420V<br>/ 440-480V - 50 Hz<br>El-forbrug 0,75 KW<br>Luft 6-8 bar. |                  |
| <b>Dimensioner:<br/>(Standardmaskine)</b> | Længde  | 2200 mm          |
|   | Bredde  | 825 mm           |
|   | Højde   | 2000 mm          |
|   | Vægt  | ca. 250 kg       |
|   | Volume.   | 4 m <sup>3</sup> |



### Functional description

The machine consists of a driven lower part and a massaging upper part which is pneumatically controlled.

The massaging effect is obtain when the hams roll between the upper and lower part, the upper part being pressure loaded. Subsequently the hams will be easier to debone.

The massage machine is shielded for safety and in compliance with the given standards.

### Specifications

|                            |   |                  |
|----------------------------|---|------------------|
| <b>Capacity:</b>           | Approx. 830 subjects/hour.<br>(830 meters/hour)   |                  |
| <b>Consumption:</b>        | Electricity 3 x 380-420V<br>/ 440-480V - 50 Hz<br>Electricity 0,75 KW<br>Airpressure 6-8 bar. |                  |
| <b>Machine dimensions:</b> | Length  | 2200 mm          |
|                            | Width   | 825 mm           |
|                            | Heigh   | 2000 mm          |
|                            | Net weight  | App.250 kg       |
|                            | Volume  | 4 m <sup>3</sup> |



**DANFOTECH**

SFK-DANFOTECH A/S  
 Indkildevej 2-4 - Postbox 821  
 DK-9100 Aalborg  
 Denmark  
 Phone: +45 98149088  
 Fax: +45 98149290